

# 58ES

## Liter

Aluminum

### ecosmart™ FREE Return Shipping Instructions:

1. Before returning cylinder, twist M/T Plug into valve. This will release any excess pressure. (Return empty cylinder to GASCO with M/T Plug installed)
2. PEEL OFF label wrap by pulling on the perforated strip. (Empty sticker is shown)
3. Generate your FREE label by using the ecosmart returns button at [www.gascogas.com](http://www.gascogas.com)
4. Prepare a box with adequate packing material and ship FREE to GASCO!

### Material

Aluminum Alloy

### Water Capacity

0.81 Liters

### Pressure

1000 psi

### Weight

1.7 lbs

### Valve Inlet

5/8-18 UNF (C10)

### Gas Type

Reactive

Non-reactive

### Dimensions

9.8" x 2.9"



# GASCO

## PRECISION GAS MIXTURE CONCENTRATION (MOLES)

COMPONENTS	CONCENTRATION (MOLES)
CARBON MONOXIDE (CO)	100 PPM
HYDROGEN SULFIDE (H2S)	25 PPM
PENTANE (C5H12)	0.35% VOL (25% LEL)
OXYGEN (O2)	19% VOL
NITROGEN (N2)	BALANCE

SDS# G-1853  
Lot # SAMPLE  
Use Before: 06/20/19  
L-SAMPLE  
1000 PSIG @ 70°F

## ecosmart™ REFILLABLE CYLINDER DO NOT DISCARD

INSTRUCTIONS ON RETURNING ecosmart CYLINDERS  
Twist the M/T Plug to ensure cylinder is empty (DOT compliant). A regulator can also be used.  
Peel off label wrap by pulling on perforated strip (empty sticker is shown).  
Generate your FREE Return Shipping Label by going to [www.gascogas.com](http://www.gascogas.com) and click on the ecosmart Return button.  
Labels will be generated and available to print through links at the top of the page.  
Ship via FEDEX with adequate and reasonable packing material.

# RETURN

# GASCO

— Calibration Gas —

Setting Standards. Exceeding Expectations.

[www.gascogas.com](http://www.gascogas.com) | 1-800-910-0051